



**Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Zinc plated Gr.B7 - Gr.2H 2.1/2X600 (23.5/8)**

Article number	22092.635.600
Brand	-
UBB	500578128984
UNSPSC	31161619
EAN	8715494320245
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	2.1/2 Inch
Length	600 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Zinc plated
Thread	8 Unified National
Threads per inch	8

Info                      Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

**Standards**

BS	≈4882
ASTM	A193/A194
ASME	B16.5/B18.2.2

B	3.3125
L (mm)	600
M	62.3

