



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Steel ASTM A320
- ASTM A194 Plain Gr.L7 -
Gr.7 2.1/2X780 (30.3/4)**

Article number	22326.635.781
Brand	-
UBB	500578328394
UNSPSC	31161619
EAN	8715494334426
PKG. of 1	Full Box Only

Technical Parameters

Diameter	2.1/2 Inch
Length	780 mm
Class	Gr.L7 - Gr.7
Material	Steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	--

Standards

ASTM	A193/A194
ASME	B16.5/B18.2.2
BS	≈4882

Technical Specification

B	3.3125
L (mm)	780

Technical Drawing

