



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Stainless steel ASTM A193 - ASTM A194 Gr.B8 Cl.2 - Gr.8 3/4X360 (14.1/4)

Article number	22529.191.361
Brand	-
UBB	500578430265
UNSPSC	31161619
EAN	8715494359726
PKG. of 1	Full Box Only

Technical Parameters

Diameter	3/4 Inch
Length	360 mm
Class	Gr.B8 Cl.2 - Gr.8
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	10
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASME	B16.5/B18.2.2
ASTM	A193/A194
BS	≈4882

Technical Specification

B	1.25
L (mm)	360

Technical Drawing

