



**Studbolt with 2 heavy  
hexagon nuts ASME B16.5/  
B18.2.2 Stainless steel ASTM  
A193 - ASTM A194 Gr.B8  
Cl.2 - Gr.8 7/8X400 (15.3/4)**

Article number	22529.222.400
Brand	-
UBB	500578439019
UNSPSC	31161619
EAN	8715494363907
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	7/8 Inch
Length	400 mm
Class	Gr.B8 Cl.2 - Gr.8
Material	Stainless steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	9
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

**Standards**

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

**Technical Specification**

B	1.4375
L (mm)	400

**Technical Drawing**

