



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Stainless steel ASTM A193 - ASTM A194 Gr.B8M Cl.2 - Gr.8M 1.3/4X430 (17)

| | |
|----------------|---------------|
| Article number | 22539.444.431 |
| Brand | - |
| UBB | 500578176322 |
| UNSPSC | 31161619 |
| EAN | 8715494313353 |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|--------------------|-----------------------|
| Diameter | 1.3/4 Inch |
| Length | 430 mm |
| Class | Gr.B8M Cl.2 - Gr.8M |
| Material | Stainless steel |
| Material technical | ASTM A193 - ASTM A194 |
| Thread direction | Right |
| Thread | 8 Unified National |
| Threads per inch | 8 |

| | |
|------|--|
| Info | Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends. |
|------|--|

Standards

| | |
|------|---------------|
| BS | ≈4882 |
| ASTM | A193/A194 |
| ASME | B16.5/B18.2.2 |

Technical Specification

| | |
|--------|------|
| B | 2.75 |
| L (mm) | 430 |
| M | 43.6 |

Technical Drawing

FABORY

