



Slotted countersunk head screw DIN 963 Steel Plain 4.8 M12X30

Article number	24539.120.030
Brand	-
UBB	500648240355
UNSPSC	31161504
EAN	8717077226678
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M12
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	963
NEN	≈2370
ISO	≈2009
NF	≈E25-123
BS	≈4183
ASME	≈B18.6.7M

Technical Specification

d-D	M12
Thread length (min.)	46
dk (max.)	22
Full thread if $L \leq$	60
k (max.)	6
L (mm)	30
n	3
P	1.75
t (min.)	2.4

Technical Drawing

