



Slotted countersunk head screw DIN 963 Steel Plain 4.8 M12X70

Article number	24539.120.070
Brand	-
UBB	500648240926
UNSPSC	31161504
EAN	8717077226739
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M12
Length	70 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	≈2370
ASME	≈B18.6.7M
NF	≈E25-123
BS	≈4183
ISO	≈2009
DIN	963

Technical Specification

d-D	M12
Thread length (min.)	46
dk (max.)	22
Full thread if $L \leq$	60
k (max.)	6
L (mm)	70
n	3
P	1.75
t (min.)	2.4

Technical Drawing

