



**Slotted countersunk head
screw DIN 963 Steel Plain 4.8
M16X45**

Article number	24539.160.045
Brand	-
UBB	500648241593
UNSPSC	31161504
EAN	8717077226791
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	45 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Plain
Thread	Metric thread

Standards

BS	≈4183
NF	≈E25-123
ASME	≈B18.6.7M
NEN	≈2370
DIN	963
ISO	≈2009

Technical Specification

d-D	M16
Thread length (min.)	58
dk (max.)	29
Full thread if $L \leq$	70
k (max.)	8
L (mm)	45
n	5
P	2
t (min.)	3.2

Technical Drawing

