



Slotted countersunk head screw DIN 963 A Steel Zinc plated 4.8 M4X18

Article number	24540.040.018
Brand	-
UBB	500645194944
UNSPSC	31161504
EAN	8717077070127
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M4
Length	18 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
BS	≈4183
NEN	≈2370
ASME	≈B18.6.7M
DIN	963
ISO	≈2009

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	18
n	1
P	0.7
t (min.)	0.8

Technical Drawing

