



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M10X20

Article number	24540.100.020
Brand	-
UBB	950353139724
UNSPSC	31161504
EAN	8715492634023
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
BS	≈4183
ASME	≈B18.6.7M
NF	≈E25-123
NEN	≈2370
DIN	963

Technical Specification

d-D	M10
Thread length (min.)	40
dk (max.)	18
Full thread if $L \leq$	50
k (max.)	5
L (mm)	20
n	2.5
P	1.5
t (min.)	2

Technical Drawing

