



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M20X40

Article number	24540.200.040
Brand	-
UBB	950353142777
UNSPSC	31161504
EAN	8715492634405
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M20
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
ISO	≈2009
NEN	≈2370
BS	≈4183
DIN	963
ASME	≈B18.6.7M

Technical Specification

d-D	M20
Thread length (min.)	70
dk (max.)	36
Full thread if $L \leq$	80
k (max.)	10
L (mm)	40
n	5
P	2.5
t (min.)	4

Technical Drawing

