



Slotted pan head screw DIN 85 Steel Plain 4.8 M5X20

Article number	24635.050.020
Brand	-
UBB	500649349825
UNSPSC	31161504
EAN	8717077265967
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M5
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Pan head
Material	Steel
Surface treatment	Plain
Thread	Metric thread

Standards

NF	≈E25-128
NEN	≈1603
DIN	85
ASME	≈B18.6.7M
BS	≈4183
ISO	≈1580

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	10
Full thread if $L \leq$	40
k (max.)	3
L (mm)	20
n	1.2
P	0.8
t (min.)	1.2

Technical Drawing

