



Cross recessed countersunk head screw Phillips DIN 965 A-H Steel Zinc plated 4.8 M6X30

Article number	24671.060.030
Brand	-
UBB	951353507670
UNSPSC	31161504
EAN	8715492642288
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M6
Length	30 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Info	F max = Maximum recommended static load (centr. tension). Approved by VdS and FM (from M10 upward only). Safety brackets necessary for VdS systems starting from DN 65.

Standards

DIN	965
ISO	≈7046-1
NF	≈E25-119-1

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if L ≤	35
k (max.)	3

Technical Drawing

L (mm) 30

No. cross recess 3

P 1

