

Cross recessed raised cheese head screw Phillips DIN 7985-H Steel Zinc plated black passivated 4.8 M8X20

Article number	24810.080.020
Brand	-
UBB	951353250826
UNSPSC	31161504
EAN	8715492645265
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M8
Length	20 mm
Class	4.8
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

DIN	7985
ISO	≈7045

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	16
Full thread if $L \leq$	40
k	6
L (mm)	20
No. cross recess	4
P	1.25

Technical Drawing

