



Cross recessed pan head tapping screw with flat end Phillips DIN 7981 F-H Steel Nickel plated ST3,5X6,5MM

Article number	26300.035.006
Brand	-
UBB	950352083394
UNSPSC	31161507
EAN	8715492654311
PKG. of 1	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	6.5 mm
Driving features	Phillips
Head shape	Pan head
Material	Steel
Surface treatment	Nickel plated
Thread	Self tapping thread

Standards

DIN	7981 F
BS	≈4174-B
ASME	≈B18.6.5M-B
NF	≈E25-658 F
ISO	≈7049 F

Technical Specification

D (mm)	3.5
dk (max.)	6.9
k	2.6
L (mm)	6.5
No. cross recess	2
P	1.3

Technical Drawing

