



Cross recessed countersunk head tapping screw Pozidriv DIN 7982 C-Z Steel Zinc plated black passivated ST2,9X9,5MM

Article number	26432.029.009
Brand	-
UBB	500654300978
UNSPSC	31161507
EAN	8712423008137
PKG. of 1	Full Box Only

Technical Parameters

Diameter	2.9 mm
Length	9.5 mm
Driving features	Pozidriv
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Self tapping thread

Info

Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	7982 CZ
ISO	7050 CZ
NF	E25-656 C

Technical Specification

D (mm)	2.9
dk	5.5
k ≈	1.7
L (mm)	9.5
No. cross recess	1
P	1.1

Technical Drawing

