



Cross recessed countersunk head tapping screw Pozidriv DIN 7982 C-Z Steel Zinc plated black passivated ST3,5X38MM

Article number	26432.035.038
Brand	-
UBB	500654301885
UNSPSC	31161507
EAN	8712423008229
PKG. of 1	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	38 mm
Driving features	Pozidriv
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Self tapping thread

Info

Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	7982 CZ
NF	E25-656 C
ISO	7050 CZ

Technical Specification

D (mm)	3.5
dk	6.8
k ≈	2.1
L (mm)	38
No. cross recess	2
P	1.3

Technical Drawing

