



HECO-FIX Cross recessed raised cheese head screw for chipboard Steel Zinc plated 3X16MM

Article number	29345.030.016
Brand	-
UBB	500500463384
UNSPSC	31161508
EAN	4019787052504
PKG. of 1	Full Box Only

Technical Parameters

Diameter	3 mm
Length	16 mm
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated

Standards

Info	All dimensions are guide values and may deviate dependent on the manufacturer. Specific features HECO-FIX PLUS screws for chipboard: Reduction of required drive torque of up to 30%. Easier handling. Substantially higher screwing performance on using storage battery screw drivers. Axial forces are reduced, thereby less wear of screw driver bits. By means of the tooth geometry, a higher unscrewing moment is nevertheless,
------	--

achieved and consequently, a secure screwed connection is obtained. Warning: electro-galvanizing of these products may cause hydrogen embrittlement.

Technical Specification

D (mm)	3
dk (max.)	5.9
k (max.)	2.2
L (mm)	16
No. cross recess	1

Technical Drawing

