



## MAXXFAST Self-drilling screw countersunk head cross recessed DIN ≈7504 O-H Steel Zinc plated ST3,9X19MM

|                |               |
|----------------|---------------|
| Article number | 30300.039.019 |
| Brand          | -             |
| UBB            | 500618323793  |
| UNSPSC         | 31161507      |
| EAN            | 8715494501798 |
| PKG. of 1      | Full Box Only |

### Technical Parameters

|                   |                     |
|-------------------|---------------------|
| Diameter          | 3.9 mm              |
| Length            | 19 mm               |
| Driving features  | Phillips            |
| Head shape        | Countersunk head    |
| Material          | Steel               |
| Surface treatment | Zinc plated         |
| Thread            | Self tapping thread |
| Info              | Full boxes only.    |

### Standards

|     |           |
|-----|-----------|
| ISO | ≈15482 H  |
| DIN | ≈7504-O H |

### Technical Specification

|                  |     |
|------------------|-----|
| D (mm)           | 3.9 |
| dk               | 8   |
| k                | 2.6 |
| L (mm)           | 19  |
| L1               | 4.5 |
| No. cross recess | 2   |

### Technical Drawing

