



MAXXFAST Zelfborende zeskantkraagbout DIN ≈7504 K Bi-Metaal ST5,5X19MM

Artikelnummer	30420.055.019
Merk	-
UBB	500618373038
UNSPSC	31162400
EAN	8715494505871
PKG. van 200	Alleen volledige verpakkingen

Technische parameters

Diameter	5.5 mm
Length	19 mm
Driving features	Hexagon
Head shape	Hexagon head
Material	Bi-Metal
Thread	Self tapping thread
Info	Full boxes only.

Standaarden

DIN	≈7504-K
ISO	≈15480

Technische specificatie

dc(max.)	11
D (mm)	5.5
k (max.) - 30410	5.4
k (max.) - 30415	5.4
k (max.) - 30420	5.45
L (mm)	19
L1	6.5
s	8

Technische tekening

