

MAXXFAST Anchor bolt
ThruMaxx Stainless steel A4
ETA-7 12X140



Article number	30553.120.140
Brand	-
UBB	500577357840
UNSPSC	31162101
EAN	8715494323482
PKG. of 1	Full Box Only

Technical Parameters

Diameter	12 mm
Length	140 mm
Material	Stainless steel
Approval	ETA Option 7
Thread	Metric thread

Info	Full boxes only.do = Nominal diameter of drill bits = Width across flatsring $\varnothing$ = Washer diameterdf = Diameter of clearance hole in the fixtureh1 = Recommended drilling depthhh(nom) = Minimum hole depthhef = Effective anchorage depthScr,N = Spacing characteristicCcr,N = Edge distance characteristicctfix(max) = Grip rangeTinst = Tightening torque in NmNrec = Recommended load in kNThe allowable load is valid for one single anchor, at non-cracked
------	---

Standards

FABORY

concrete (pressure zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr, N are taken in to account. ETA-7

Technical Specification

Ccr, N	98
d-D	M12
df	14
D (mm)	12
do	12
h (nom.)	77
h1	85
hef	65
L (mm)	140
Nrec	9.92
Ring ø	24
s	19
Scr, N	195
tfix(max.)	48
Tinst	60

Technical Drawing

