

MAXXFAST Hammerset
anchor Stainless steel A4 M6



Article number	30576.060.001
Brand	-
UBB	500619771826
UNSPSC	31162101
EAN	8715494136433
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M6
Material	Stainless steel
Thread	Metric thread
Type no.	D-MAXX A4

Info	do= Nominal diameter of drill bitdw= Diameter of clearance hole in the fixtureh1= Depth of drilled hole to deepest pointhc= Minimal thickness of concrete elemente = Bolt length to be threadedSmin.= Minimal spacingCmin.= Minimal edge distanceNrec= Recommended load in kNTinst= Tightening torque in NmThe allowable load (Nrec) is valid for one single anchor, at non-cracked concrete (pressure zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Smin.and
------	--

Standards

Cmin.are taken in to account.

FABORY

Technical Specification

Cmin.	105
d-D	M6
do	8
dw	7
e (max.)	10
e (min.)	6
h1	27
hc	100
L (mm)	25
Nrec	2.08
Smin.	60
Tinst	4

Technical Drawing

