



Taper pin with internal thread, ground DIN 7978 A
Free-cutting steel 20X90MM

Article number	39012.200.090
Brand	-
UBB	500644918012
UNSPSC	31163205
EAN	8717077041226
PKG. of 1	Full Box Only

Technical Parameters

Diameter	20 mm
Length	90 mm
Material	Free-cutting steel
Info	The nominal length (L, tolerance class js15) includes the rounded ends.

Standards

NF	≈E27-479
DIN	7978-A
NEN	≈2463
ISO	≈8736-A

Technical Specification

a ≈	2.5
d1	20
d2	12
D (mm)	20
L (mm)	90
r ≈	12
t1	18

Technical Drawing

