



Parallel pin (dowel pin) hardened, m6 DIN 6325 Steel 60±2HRC Plain 1X8MM

Article number	39080.010.008
Brand	-
UBB	950359020225
UNSPSC	31163203
EAN	8715492798343
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1 mm
Length	8 mm
Material	Steel
Material technical	60±2HRC
Surface treatment	Plain

Info

Parallel pins are used mainly as dowels for tools, clamping devices and measuring devices. The nominal length (L#, tolerance class js14) includes the rounded ends.

Standards

DIN	6325
ISO	≈8734-A
NF	≈E27-475
NEN	≈2282

Technical Specification

D (mm)	1
L (mm)	8
L1	8
L2	0.4
r	1
z1 ≈	0.15
z2 ≈	0.08

Technical Drawing

