

Parallel key high type DIN 6885 A Steel C45+C Plain 20X12X250MM



Article number	39250.212.250
Brand	-
UBB	500647166601
UNSPSC	31163207
EAN	8717077089365
PKG. of 1	Full Box Only

Technical Parameters

Length	250 mm
Material	Steel
Material technical	C45+C
Surface treatment	Plain
Info	Tolerance classes for dimensions b and h according to DIN 6880.

Standards

ISO	R773
NEN	2430
BS	4235-1
DIN	6885-A

Technical Specification

b	20
For shaft $\varnothing$	65
For shaft $\varnothing \leq$	75
h	12
L (mm)	250

Technical Drawing

