



**NORMA Hose clamp two parts, band width 20 mm
Steel Zinc plated 79-87MM**

Article number	43025.079.087
Brand	-
UBB	950553066099
UNSPSC	31162906
EAN	8715492830944
PKG. of 1	Full Box Only

Technical Parameters

Material	Steel
Surface treatment	Zinc plated
Info	Band steel heavy zinc plated with a layer thickness of min. 18µm.

Standards

Technical Specification

B	20
Clamping range (mm)	79-87
S	1

Technical Drawing

