

Dormer Jobber drill A100
DIN 338 HSS Vaporised
3.10mm



Article number	4G826819
Brand	-
UBB	500630801180
UNSPSC	23241639
EAN	7320760001615
PKG. of 1	Full Box Only

Technical Parameters

Total length	65
Diameter drill	3.1
Holding system	Cylindrical plug-in axle
Cutting length	36
Cutting material	HSS
Shank shape	Cylindrical
Spiral drill	Yes

Standards