

Hexagon head bolt DIN 931 Stainless steel A2 Min.50 M10X340

Article number	51000.100.340
Brand	-
UBB	500571244010
UNSPSC	31161620
EAN	8715494134323
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	340 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

NEN	1555
ASME	B18.2.3.1M
NF	E25-112
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	340
P	1.5
s	17

Technical Drawing

