

Hexagon head bolt DIN 931 Stainless steel A2 Min.50 M27X120

Article number	51000.270.120
Brand	-
UBB	950351770702
UNSPSC	31161620
EAN	8715492252142
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M27
Length	120 mm
Class	Min.50
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50.

Standards

DIN	931
ISO	4014
NEN	1555
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79
b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	120
P	3
s	41

Technical Drawing

