



**Hexalobular socket button
head screw ISO ≈7380-1
Stainless steel A2 M10X12**

Article number	51029.100.012
Brand	-
UBB	500635833923
UNSPSC	31161518
EAN	8715494553827
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	12 mm
Driving features	Hexalobular
Head shape	Button head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

Standards

ISO	≈7380-1
NF	≈E25-126
BS	≈4168-6
ASME	≈B18.3.4M

Technical Specification

d-D	M10
dk (max.)	17.5
k (max.)	5.5
L (mm)	12
P	1.5
Socket	50

Technical Drawing

