



Threaded rod length 3 meter
DIN 976-1A Stainless steel
A2 70 M20

Article number	51072.200.001
Brand	-
UBB	500621786168
UNSPSC	31161618
EAN	8715494512343
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M20
Length	3000 mm
Class	70
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M3 or M24 are minimal property class 50.3 meter

Standards

DIN	976-1A
NF	E25-136

Technical Specification

d-D	M20
L (mm)	3000
P	2.5

Technical Drawing

