



Slotted countersunk head screw DIN 963 Stainless steel A2 70 M5X22

Article number	51110.050.022
Brand	-
UBB	500571317113
UNSPSC	31161504
EAN	8715494116374
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M5
Length	22 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-123
ISO	≈2009
NEN	≈2370
BS	≈4183
ASME	≈B18.6.7M
DIN	963

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	22
n	1.2
P	0.8
t (min.)	1

Technical Drawing

