



Slotted countersunk head screw DIN 963 Stainless steel A2 70 M10X20

Article number	51110.100.020
Brand	-
UBB	950353253236
UNSPSC	31161504
EAN	8715492269966
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	20 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

BS	≈4183
NF	≈E25-123
ASME	≈B18.6.7M
NEN	≈2370
DIN	963
ISO	≈2009

Technical Specification

d-D	M10
Thread length (min.)	40
dk (max.)	18
Full thread if $L \leq$	50
k (max.)	5
L (mm)	20
n	2.5
P	1.5
t (min.)	2

Technical Drawing

