



Slotted cheese head screw DIN 84 Stainless steel A2 small pack M3X50

Article number	51121.030.050
Brand	-
UBB	951353518982
UNSPSC	31161504
EAN	8715492272669
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M3
Length	50 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread
Info	small pack

Standards

ISO	≈1207
BS	≈4183
ASME	≈B18.6.7M
NEN	≈1602
NF	≈E25-127
DIN	84

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	5.5
Full thread if L ≤	30
k (max.)	2
L (mm)	50
n	0.8
P	0.5
t (min.)	0.85

Technical Drawing