



Slotted pan head screw DIN 85 Stainless steel A2 70 M3X10

Article number	51140.030.010
Brand	-
UBB	950353265784
UNSPSC	31161504
EAN	8715492272942
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M3
Length	10 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈1580
ASME	≈B18.6.7M
NF	≈E25-128
DIN	85
BS	≈4183
NEN	≈1603

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	6
Full thread if $L \leq$	30
k (max.)	1.8
L (mm)	10
n	0.8
P	0.5
t (min.)	0.7

Technical Drawing

