



Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M8X60

Article number	51230.080.060
Brand	-
UBB	500571475929
UNSPSC	31161518
EAN	8715494114127
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M8
Length	60 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A2
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

NEN	2344
BS	4168-4
DIN	915
ASME	B18.3.6M
NF	E27-182
ISO	4028

Technical Specification

d-D	M8
dp (max.)	5.5
L (mm)	60
P	1.25
s	4
t (min.)	3
z long (min.)	4
z long if L ≥	12
z short (min.)	2

Technical Drawing

