



Hexagon socket set screw with dog point DIN 915 Stainless steel A2 M10X16

Article number	51230.100.016
Brand	-
UBB	952351512308
UNSPSC	31161518
EAN	8715492276384
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	16 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A2
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

NF	E27-182
NEN	2344
ASME	B18.3.6M
DIN	915
ISO	4028
BS	4168-4

Technical Specification

d-D	M10
dp (max.)	7
L (mm)	16
P	1.5
s	5
t (min.)	4
z long (min.)	5
z long if L ≥	16
z short (min.)	2.5

Technical Drawing

