



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M1,6X6

Article number	51300.016.006
Brand	-
UBB	500571330140
UNSPSC	31161504
EAN	8715494115407
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M1.6
Length	6 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-119-1
ISO	≈7046-1
DIN	965

Technical Specification

d-D	M1.6
Thread length (min.)	15
dk (max.)	3
Full thread if $L \leq$	16
k (max.)	0.96
L (mm)	6
No. cross recess	0
P	0.35

Technical Drawing

