



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M4X5

Article number	51300.040.005
Brand	-
UBB	500571331130
UNSPSC	31161504
EAN	8715494115506
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M4
Length (L) (mm)	5

Standards

ISO	7046-2-H
DIN	965 A-H
NF	E25-119-2

Technical Specification

Thread length (min.)	22
d_k (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
No. cross recess	2
P	0.70

Technical Drawing

