



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M4X8

Article number	51300.040.008
Brand	-
UBB	950353276831
UNSPSC	31161504
EAN	8715492281302
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M4
Length (L) (mm)	8

Standards

DIN	965 A-H
NF	E25-119-2
ISO	7046-2-H

Technical Specification

Thread length (min.)	22
d_k (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
No. cross recess	2
P	0.70

Technical Drawing

