



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M4X12

Article number	51300.040.012
Brand	-
UBB	950353277094
UNSPSC	31161504
EAN	8715492281326
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M4
Length	12 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	965
ISO	≈7046-1
NF	≈E25-119-1

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	12
No. cross recess	2
P	0.7

Technical Drawing

