

Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A2 M6X50



Article number	51300.060.050
Brand	-
UBB	950353552215
UNSPSC	31161504
EAN	8715492281678
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	50

Standards

ISO	7046-2-H
NF	E25-119-2
DIN	965 A-H

Technical Specification

Thread length (min.)	28
d_k (max.)	11
Full thread if $L \leq$	35
k (max.)	3
No. cross recess	3
P	1

Technical Drawing

