

## Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M3X16



Article number	51302.030.016
Brand	-
UBB	951353119344
UNSPSC	31161504
EAN	8715492282156
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	16

### Standards

ISO	7046-2-Z
NF	E25-119-2
DIN	965 A-Z

### Technical Specification

Thread length (min.)	19
$d_k$ (max.)	5.6
Full thread if $L \leq$	22
$k$ (max.)	1.65
No. cross recess	1
P	0.50

### Technical Drawing

