

## Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M4X10



Article number	51302.040.010
Brand	-
UBB	951353120235
UNSPSC	31161504
EAN	8715492282231
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M4
Length (L) (mm)	10

### Standards

DIN	965 A-Z
NF	E25-119-2
ISO	7046-2-Z

### Technical Specification

Thread length (min.)	22
$d_k$ (max.)	7.5
Full thread if $L \leq$	25
$k$ (max.)	2.2
No. cross recess	2
P	0.70

### Technical Drawing

