

## Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M4X40



Article number	51302.040.040
Brand	-
UBB	951353120987
UNSPSC	31161504
EAN	8715492282309
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M4
Length (L) (mm)	40

### Standards

NF	E25-119-2
DIN	965 A-Z
ISO	7046-2-Z

### Technical Specification

Thread length (min.)	22
$d_k$ (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
No. cross recess	2
P	0.70

### Technical Drawing

