



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M4X50

Article number	51302.040.050
Brand	-
UBB	951353121068
UNSPSC	31161504
EAN	8715492282316
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M4
Length	50 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	965
ISO	≈7046-1
NF	≈E25-119-1

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if L ≤	25
k (max.)	2.2
L (mm)	50
No. cross recess	2
P	0.7

Technical Drawing

