



Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A2 M8X35

Article number	51302.080.035
Brand	-
UBB	500571335685
UNSPSC	31161504
EAN	8715494112628
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M8
Length	35 mm
Class	70
Driving features	Pozidriv
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-119-1
ISO	≈7046-1
DIN	965

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
Full thread if L ≤	40
k (max.)	4
L (mm)	35
No. cross recess	4
P	1.25

Technical Drawing

