

Cross recessed raised cheese head screw Phillips DIN 7985-H Stainless steel A2 M4X4

Article number	51340.040.004
Brand	-
UBB	500633235006
UNSPSC	31161504
EAN	8715494592420
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M4
Length	4 mm
Class	70
Driving features	Phillips
Head shape	Raised cheese head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈7045
DIN	7985

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	8
Full thread if L ≤	25
k	3.1
L (mm)	4
No. cross recess	2
P	0.7

Technical Drawing

