



## Retaining ring for shafts - normal type DIN 471 Stainless spring steel 1.4122 / 1.4021 8MM

Article number 51435.008.001

Brand -

UBB 950357143102

UNSPSC 31163202

EAN 8715492289575

PKG. of 1 Full Box Only

### Technical Parameters

Diameter	8 mm
For nom. size	8mm
Material	Stainless spring steel
Material technical	1.4122/1.4021
Nom. size shaft d1	8

#### Info

Other types of stainless steel than specified (but with equal properties) may be supplied at the discretion of the manufacturer. Avoid contact with chloride containing (cleaning-) liquids in order to reduce the risk of chloride induced stress corrosion cracking. d4 is the minimum required installation space. During assembly it is essential to not overspread the rings, a maximum spread of  $1,01 \times d1$  is recommended. For

### Standards

NF	E22-163
DIN	471
BS	3673-4

**FABORY** proper installation  
use pliers with  
spread limiter or  
assemble the aid of  
a cone.

## Technical Specification

Groove d2	7.6
Groove m (H13)	0.9
Groove n (min.)	0.6
Ring d3	7.4
Ring d4	14.7
Ring s	0.8
Ring b $\approx$	1.5

## Technical Drawing

