



Retaining ring for shafts - normal type DIN 471 Stainless spring steel 1.4122 / 1.4021 36MM

Article number	51435.036.001
Brand	-
UBB	950357356209
UNSPSC	31163202
EAN	8715492289827
PKG. of 1	Full Box Only

Technical Parameters

Diameter	36 mm
For nom. size	36mm
Material	Stainless spring steel
Material technical	1.4122/1.4021
Nom. size shaft d1	36

Info

Other types of stainless steel than specified (but with equal properties) may be supplied at the discretion of the manufacturer. Avoid contact with chloride containing (cleaning-) liquids in order to reduce the risk of chloride induced stress corrosion cracking. d4 is the minimum required installation space. During assembly it is essential to not overspread the rings, a maximum spread of 1,01 x d1 is recommended. For

Standards

NF	E22-163
DIN	471
BS	3673-4

FABORY proper installation
use pliers with
spread limiter or
assemble the aid of
a cone.

Technical Specification

Groove d2	34
Groove m (H13)	1.85
Groove n (min.)	3
Ring d3	33.2
Ring d4	47.8
Ring s	1.75
Ring b \approx	4

Technical Drawing

